



## FEMTIS<sup>®</sup> Mplus<sup>toric</sup>

### FB-313 MF30T0-T3

One-piece multifocal-toric posterior chamber lens for extended depth of focus and high contrast sensitivity with aspherical surface for fixation in the automated continuous circular capsulotomy

<b>Product</b>	FEMTIS <sup>®</sup> Mplus <sup>toric</sup> FB-313 MF30T0-T3	multifocal-toric
		Auto-CCC
		aspheric
<b>Type</b>	Foldable one-piece multifocal-toric IOL for capsular bag and additional capsulotomy fixation	
<b>Optic Size</b>	5.7 mm	
<b>Overall Length</b>	10.5 mm	
<b>Haptic Angulation</b>	0°	
<b>Optic Design</b>	Biconvex Sector-shaped near vision segment - anterior: +3.0D Aspherical and toric surface -posterior Spherical aberration neutral	
<b>IOL Design</b>	Plate haptic with additional Clip-haptics Optic and haptic with square edges	
<b>Material</b>	HydroSmart <sup>®</sup> - a copolymer, consisting of hydrophilic acrylates with hydrophobic surface UV absorbing	
<b>Available Diopters</b>	SE +15.0D to +30.0D (0.5D) cyl.: T0 +0.75D   T1 +1.5D   T2 +2.25D   T3 +3.0D	
<b>Refractive Index</b>	1.46	
<b>A-Constant (nominal)</b>	117.8	
<b>Sterilisation</b>	Steam sterilisation	
<b>Storage</b>	Supplied at sterile water	
<b>Recommended Injector-Sets</b>	Check compatibility of IOL with injector matrix provided at <a href="http://www.lentis-eifu.com">www.lentis-eifu.com</a>	

Revision: QF2263v2